



Stepladder with platform, single-sided access, Number of steps including platform: 10



Order data

Order number	966272 10
GTIN	4003866404797
Item class	96Z

Description

Version:

Stepladder with flanged steps 80 mm deep. Large working platform with aluminium chequer plate covering (380×390 mm). Aluminium storage tray. 2 handrails as standard, for safe ascent and descent. Optimum stability due to 2 high-strength perlon belts that prevent splay (from 5 treads).

Standard:

EN 131.

Technical description

Working height approx.	4.6 m
Weight	20 kg
Platform depth	390 mm
Platform width	380 mm
Rung/step depth	80 mm

Belt to prevent splay	2 high-strength Perlon belts
Handrail	2
Number of steps including platform	10
Platform height without railing	2.59 m
outer width at bottom	0.8 m
Standard	EN 131
Accessibility	single-sided
Storage tray available	yes
Cross beam height	73 mm
Ladder length	1.43 m
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder