



Folding platform, standard version, Platform height: 4500 mm



Order data

Order number	966310 4500
GTIN	4003866537655
Item class	96Y

Description

Version:

Frame width 0.68 m;

Frame length 1.80 m.

Can be extended using standard parts.

Folding base module for quick assembly / disassembly.

Minimal space required for transport and storage.

Roller castors Ø 125 mm, with pins (not height-adjustable). Platform **with** step-through flap.

Description:

Range Z 600 / Z 500

Feature:

Range Z 600 / Z 500

Standard:

DIN EN 1004

Ladders and platforms load capacity: 200 kg

Working height approx.: 6.5 m

Scaffolding height: 5.85 m

Weight: 108.9 kg

Technical description

Working height approx.	6.5 m
Platform version	with step-through flap
Platform height	4500 mm
Scaffolding length	1.8 m
Norm	DIN EN 1004
Scaffolding height	5.85 m
Scaffolding width	0.68 m
Weight	108.9 kg
Castors Ø	125 mm
Ladders and platforms load capacity	200 kg