



Platform steps mobile, double-sided access, Number of steps including platform: 4



Order data

Order number	966270 4
GTIN	4003866419821
Item class	96Z

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° rise angle). Spacious platform (600×800 mm) with platform railing (1.00 m high) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

Number of castors without parking brake	2
Accessibility	double-sided
Step inclination	60 degrees
Standard	DIN EN 131-7

Platform width	600 mm
Number of steps including platform	4
Rung/step depth	200 mm
Weight	36 kg
Platform height without railing	0.96 m
Footprint depth	1.79 m
with platform railings	yes
Castors Ø	125 mm
Footprint width	0.82 m
Platform depth	800 mm
Number of castors with parking brake	2
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps