



Platform steps mobile, single-sided access, Number of steps including platform: 4



Order data

Order number	966220 4
GTIN	4003866419722
Item class	96Z

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° angle of inclination). Spacious platform (600×800 mm) with platform guardrail (at a height of 1.00 m) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

Rung/step depth	200 mm
Platform width	600 mm
Castors Ø	125 mm
Number of steps including platform	4

Number of castors without parking brake	2
Weight	31.8 kg
Platform depth	800 mm
Footprint width	0.82 m
Footprint depth	1.45 m
Accessibility	single-sided
Step inclination	60 degrees
Platform height without railing	0.96 m
Number of castors with parking brake	2
Standard	DIN EN 131-7
with platform railings	yes
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps