



## Stepladder with platform, single-sided access, Number of steps including platform: 12



### Order data

|              |               |
|--------------|---------------|
| Order number | 966272 12     |
| GTIN         | 4003866416356 |
| Item class   | 96Z           |

### Description

#### Version:

Stepladder with flanged steps 80 mm deep. Large working platform with aluminium chequer plate covering (380×390 mm). Aluminium storage tray. 2 handrails as standard, for safe ascent and descent. Optimum stability due to 2 high-strength perlon belts that prevent splay (from 5 treads).

#### Standard:

EN 131.

### Technical description

|                                 |        |
|---------------------------------|--------|
| Working height approx.          | 5.1 m  |
| Platform depth                  | 390 mm |
| Platform height without railing | 3.11 m |
| Storage tray available          | yes    |
| Rung/step depth                 | 80 mm  |

|                                     |                              |
|-------------------------------------|------------------------------|
| Belt to prevent splay               | 2 high-strength Perlon belts |
| Number of steps including platform  | 12                           |
| Platform width                      | 380 mm                       |
| outer width at bottom               | 0.86 m                       |
| Handrail                            | 2                            |
| Weight                              | 22 kg                        |
| Accessibility                       | single-sided                 |
| Standard                            | EN 131                       |
| Ladders and platforms load capacity | 150 kg                       |
| Two hands free principle            | yes                          |
| Safer Step                          | yes                          |
| Type of product                     | Platform ladder              |