



Folding platform, standard version, Platform height: 5650 mm



Order data

Order number	966310 5650
GTIN	4003866537662
Item class	96Y

Description

Version:

Frame width 0.68 m;

Frame length 1.80 m.

Can be extended using standard parts.

Folding base module for quick assembly / disassembly.

Minimal space required for transport and storage.

Roller castors Ø 125 mm, with pins (not height-adjustable). Platform **with** step-through flap.

Description:

Range Z 600 / Z 500

Feature:

Range Z 600 / Z 500

Standard:

DIN EN 1004

Ladders and platforms load capacity: 200 kg

Working height approx.: 7.65 m

Scaffolding height: 6.7 m

Weight: 140.9 kg

Technical description

Working height approx.	7.65 m
Scaffolding width	0.68 m
Platform version	with step-through flap
Castors Ø	125 mm
Norm	DIN EN 1004
Scaffolding height	6.7 m
Weight	140.9 kg
Platform height	5650 mm
Scaffolding length	1.8 m
Ladders and platforms load capacity	200 kg