



Platform steps mobile, double-sided access, Number of steps including platform: 5



Order data

| | |
|--------------|---------------|
| Order number | 966270 5 |
| GTIN | 4003866419838 |
| Item class | 96Z |

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° rise angle). Spacious platform (600×800 mm) with platform railing (1.00 m high) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

| | |
|------------------------------------|------------|
| Platform height without railing | 1.2 m |
| Platform width | 600 mm |
| Step inclination | 60 degrees |
| Number of steps including platform | 5 |

| | |
|---|----------------|
| Platform depth | 800 mm |
| Weight | 41 kg |
| Standard | DIN EN 131-7 |
| Accessibility | double-sided |
| Footprint depth | 2.06 m |
| Number of castors without parking brake | 2 |
| Castors Ø | 125 mm |
| Number of castors with parking brake | 2 |
| Rung/step depth | 200 mm |
| with platform railings | yes |
| Footprint width | 0.87 m |
| Type of step | Step |
| Knee bar | yes |
| Ladders and platforms load capacity | 150 kg |
| Two hands free principle | yes |
| Type of product | Platform steps |