



Safemaster S fold-away platform ladder, Number of steps including platform: 5



Order data

Order number	966275 5
GTIN	4003866416752
Item class	96Z

Description

Version:

Compact platform ladder with 80 mm deep rungs. Work platform (400×400 mm) with guard rails around 3 sides and storage tray. Optimum stability due to rigid locking bar on both sides.

Standard:

EN 131

Technical description

Accessibility	single-sided
Knee bar	no
Standard	EN 131
Number of steps including platform	5
Rung/step depth	80 mm
Handrail	2
Storage tray available	yes
Weight	14.4 kg

Platform width	400 mm
Platform height without railing	1.32 m
Belt to prevent splay	double-sided, rigid connection
Platform depth	400 mm
Footprint depth	1.25 m
Footprint width	0.68 m
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder