



Platform steps mobile, double-sided access, Number of steps including platform: 6



Order data

Order number	966270 6
GTIN	4003866419845
Item class	96Z

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° rise angle). Spacious platform (600×800 mm) with platform railing (1.00 m high) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

Platform depth	800 mm
Number of castors with parking brake	2
Number of steps including platform	6
Accessibility	double-sided

Platform height without railing	1.44 m
Standard	DIN EN 131-7
Platform width	600 mm
Rung/step depth	200 mm
Footprint width	0.93 m
Footprint depth	2.34 m
Step inclination	60 degrees
Number of castors without parking brake	2
Castors Ø	125 mm
Weight	46 kg
with platform railings	yes
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps