



Safemaster S fold-away platform ladder, Number of steps including platform: 6



Order data

Order number	966275 6
GTIN	4003866416769
Item class	96Z

Description

Version:

Compact platform ladder with 80 mm deep rungs. Work platform (400×400 mm) with guard rails around 3 sides and storage tray. Optimum stability due to rigid locking bar on both sides.

Standard:

EN 131

Technical description

Footprint width	0.71 m
Accessibility	single-sided
Handrail	2
Number of steps including platform	6
Standard	EN 131
Platform depth	400 mm
Knee bar	no
Platform width	400 mm

Weight	16.1 kg
Rung/step depth	80 mm
Belt to prevent splay	double-sided, rigid connection
Footprint depth	1.42 m
Platform height without railing	1.58 m
Storage tray available	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder