



## Sheet metal slitter / shears, Type: 723031



### Order data

Order number	078102 723031
GTIN	4014586874661
Item class	03F

### Description

#### Version:

#### Sheet metal slitter.

- Distortion-free cut.
- Open cutting head for best view on to the cut.
- QuickIN quick-change system for quick blade changing without tools or adjustment.

### Technical description

Power consumption	350 W
Cutting width	5 mm
Manufacturer's designation	BSS 1.6 CE
Weight	1.4 kg
maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	0.8 mm
Rate of strokes	3800 min <sup>-1</sup>
Radius of the smallest curve	90 mm
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Cutting speed	6 - 10 m/min
Cable length	5 m

maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.6 mm
Power supply	Mains-powered
Type of product	Scissors