



## Disposable gloves pack Dermatril P 743, Glove size: 9



### Order data

Order number	094725 9
GTIN	4008198774396
Item class	04Q

### Description

#### Version:

Disposable glove set **in dispenser**. Category III. Powder-free.

Dermatril P 743. Higher chemical and mechanical resistance than 094730 (740). Therefore, the gloves can be used for longer and offer protection against a wider spectrum of hazardous substances. Approved for contact with foodstuffs. Free of latex. With long gauntlet. AQL 0.65 (EN 374-2).

With roughened finger tips.

#### Standard:

EN 374; EN 455

### Technical description

Wall thickness	0.2 mm
Manufacturer's designation	Dermatril P 743
Glove size	9
Permeation time for acetonitrile 99 %	<10 min

Permeation time for acetone 99 %	<10 min
Permeation time for cyclohexane 99 %	30-40 min
Permeation time for dimethyl sulphoxide 99 %	10-30 min
Permeation time for ethanol 95 %	10-30 min
Permeation time for isopropanol 99 %	10-30 min
Permeation time for methanol 99 %	<10 min
Permeation time for sodium hydroxide 40 %	240-480 min
Permeation time for sodium hydroxide 50 %	240-480 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for sulphuric acid 96 %	10-30 min
Protection category	Category III
Type of glove	Disposable glove
EN	EN 374
Glove characteristics	DMF-free
Glove characteristics	free of latex
Glove characteristics	Foodstuffs certified
EN 374	Type A (JKLOPT)
Resistance to chemicals	JKLOPT
Material	Nitrile
electrostatic characteristic	0.2 sec. in accordance with charge decay specifications in EN 61340-5-1
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
Backing material	Nitril
Thickness	0.2 mm
Length	280 mm
Contents	50
Colour	blue
Application range	Precision
Cut protection class	0

AQL	0.65
Application	disposable
Type of product	Disposable glove