

Ansell**Disposable gloves pack TouchNTuff® 92-670, Glove size: 8****Order data**

| | |
|--------------|--------------|
| Order number | 094720 8 |
| GTIN | 076490493332 |
| Item class | 04P |

Description**Version:**

Disposable glove set **in dispenser**. Category III. Powder-free. TouchNTuff® 92-670. Free of silicones and waxes. Textured fingertips. Approved for contact with food. AQL 1.5 (EN 374-2).

Standard:

EN 374

Technical description

| | |
|-------------------------------------------|-----------|
| Glove size | 8 |
| Wall thickness | 0.1 mm |
| Permeation time for cyclohexane 99 % | >480 min |
| Permeation time for ethanol 95 % | <10 min |
| Permeation time for isopropanol 99 % | 30-40 min |
| Permeation time for sodium hydroxide 40 % | >480 min |
| Permeation time for sulphuric acid 50 % | >480 min |

| | |
|-------------------------|----------------------------------------------------|
| Series | TouchNTuff® |
| Protection category | Category III |
| Type of glove | Disposable glove |
| Glove characteristics | Foodstuffs certified |
| Glove characteristics | Silicone-free |
| Glove characteristics | free of latex |
| Glove characteristics | Suitable for allergy sufferers |
| EN 374 | Type B (JKT) |
| Resistance to chemicals | JKT |
| Material | Nitrile |
| Protection class | Schutz gegen bakteriologische Risiken gemäß EN 374 |
| Backing material | Nitril |
| Coating | Nitril |
| Thickness | 0.11 mm |
| Length | 240 mm |
| Contents | 100 |
| Weight | 3 g |
| Colour | blue |
| Application range | Precision |
| AQL | 1.5 |
| Application | disposable |
| Type of product | Disposable glove |