

ASATEX™

Pair of cold protection gloves 3677V, Glove size: 10


Order data

Order number	094811 10
GTIN	4029201140847
Item class	09H

Description

Version:

3677V. Gloves with **very warm and pleasant acrylic lining**. Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

Standard:

3677V. Gloves with **very warm and pleasant acrylic lining**. Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
Colour: black

Technical description

silicone-free	yes
DMF-free	yes
Oil grip	good
Glove size	10
Heat protection	not available
EN 388 abrasion resistance	3
EN 388 penetration resistance	1
EN 388 cut resistance	2
EN 388 tear propagation resistance	2
Lining material	Acrylic
Accuracy of fit	very good
Cold protection	good
Touch sensitivity	not available
Material of coating	PVC
Wet grip	good
Breathability	not available
Type of glove	Cold protection gloves
Protection category	Category II
Glove characteristics	DMF-free
Glove characteristics	Silicone-free
Contents	6
Application	reusable
Application range	All-round
EN 388:2016	3131X
EN 511	010
Backing material	Polyamide / acrylic
Coating	HPT/vinyl
Coating variant	3/4 coating
Colour	black

Weight	53 g
Type of product	Cold protection gloves