

Ansell**Disposable gloves pack TouchNTuff® 92-600, Glove size: 8****Order data**

Order number	094721 8
GTIN	076490493370
Item class	04P

Description**Version:**

Disposable glove set **in dispenser**. Category III. Powder-free. TouchNTuff® 92-600. Free of latex - no risk of type-I allergies. Smooth grip profile. Approved for contact with foodstuffs. AQL 1.5 (EN 374-2).

Standard:

EN 374

Technical description

Glove size	8
Wall thickness	0.12 mm
Permeation time for acetonitrile 99 %	<10 min
Permeation time for cyclohexane 99 %	>480 min
Permeation time for dimethyl sulphoxide 99 %	<10 min
Permeation time for ethanol 95 %	<10 min
Permeation time for isopropanol 99 %	60-120 min

Permeation time for sodium hydroxide 50 %	>480 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for sulphuric acid 96 %	<10 min
Series	TouchNTuff®
Protection category	Category III
Type of glove	Disposable glove
Glove characteristics	Foodstuffs certified
Glove characteristics	free of latex
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Silicone-free
EN 374	Type B (JKPT)
Resistance to chemicals	JKPT
Material	Nitrile
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
Backing material	Nitril
Coating	Nitril
Thickness	0.13 mm
Length	240 mm
Contents	100
Weight	3.1 g
Colour	green
Application range	Precision
AQL	1.5
Application	disposable
Type of product	Disposable glove