

ASATEX™

Pair of cold protection gloves 3677V, Glove size: 11


Order data

Order number	094811 11
GTIN	4029201140854
Item class	09H

Description

Version:

3677V. Gloves with **very warm and pleasant acrylic lining.** Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

Standard:

3677V. Gloves with **very warm and pleasant acrylic lining.** Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
Colour: black

Technical description

EN 388 abrasion resistance	3
silicone-free	yes
Glove size	11
Breathability	not available
Wet grip	good
Accuracy of fit	very good
Cold protection	good
EN 388 penetration resistance	1
Material of coating	PVC
Oil grip	good
Lining material	Acrylic
EN 388 tear propagation resistance	2
Touch sensitivity	not available
DMF-free	yes
EN 388 cut resistance	2
Heat protection	not available
Protection category	Category II
Type of glove	Cold protection gloves
Glove characteristics	DMF-free
Glove characteristics	Silicone-free
Contents	6
Application	reusable
Application range	All-round
EN 388:2016	3131X
EN 511	010
Backing material	Polyamide / acrylic
Coating	HPT/vinyl
Coating variant	3/4 coating
Colour	black

Weight	53 g
Type of product	Cold protection gloves