



Disposable gloves pack Dermatril 740, Glove size: 10



Order data

Order number	094730 10
GTIN	4008198774006
Item class	04Q

Description

Version:

Disposable glove set **in dispenser**. Category III. Powder-free.
Dermatril 740. Approved for contact with foodstuffs. Free of latex. AQL 0.65 (EN 374-2).

Contents: 100 pieces.

With roughened finger tips.

Standard:

EN 374; EN 455

Technical description

Glove size	10
Wall thickness	0.11 mm
Permeation time for acetonitrile 99 %	<10 min
Permeation time for acetone 99 %	<10 min
Permeation time for cyclohexane 99 %	30-40 min
Permeation time for dimethyl sulphoxide 99 %	10-30 min

Permeation time for ethanol 95 %	10-30 min
Permeation time for isopropanol 99 %	10-30 min
Permeation time for methanol 99 %	<10 min
Permeation time for sodium hydroxide 40 %	240-480 min
Permeation time for sodium hydroxide 50 %	240-480 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for sulphuric acid 96 %	10-30 min
Protection category	Category III
Type of glove	Disposable glove
Glove characteristics	DMF-free
Glove characteristics	Foodstuffs certified
Glove characteristics	free of latex
EN 374	Typ B (KPT)
Resistance to chemicals	KPT
Material	Nitrile
electrostatic characteristic	0.1 sec. in accordance with charge decay specifications in EN 61340-5-1
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
Backing material	Nitril
Thickness	0.11 mm
Length	250 mm
Contents	100
Colour	blue
Application range	Precision
Standard/regulation	EN 374
AQL	0.65
Application	disposable
Type of product	Disposable glove

