



Pair of chemical protective gloves UltraNeo 450, Glove size: 7



Order data

Order number	094770 7
GTIN	3245424503172
Item class	06D

Description

Version:

Category III safety gloves.

UltraNeo 450. Neoprene gloves with medium chemical protection. Good grip security due to non-slip profile, suppleness and finger freedom. Protection of the forearm due to the long cuff.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
EN 374:2016: Type A (ALMNST)

Technical description

Permeation time for acetone 99 %	10-30 min
Permeation time for sulphuric acid 96 %	120-240 min
Permeation time for ethanol 95 %	240-480 min
Wall thickness	0.75 mm
Glove size	7
Permeation time for cyclohexane 99 %	30-40 min

Permeation time for dimethyl sulphoxide 99 %	240-480 min
Permeation time for acetonitrile 99 %	10-30 min
Permeation time for isopropanol 99 %	>480 min
Permeation time for methanol 99 %	120-240 min
Permeation time for sodium hydroxide 40 %	>480 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for sodium hydroxide 50 %	>480 min
Lining material	natural latex
Type of glove	Chemicals protection gloves
Protection category	Category III
Contents	50
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374:2016	Type A (ALMNST)
Resistance to chemicals	ALMNST
EN 388:2016	2121X
Material	Neoprene, latex
Backing material	Neoprene, latex
AQL	0,65
Length	410 mm
Thickness	0.75 mm
Colour	black
Application	reusable
Standard/regulation	EN 374
Type of product	Chemicals protection gloves