

**uvex****Pair of chemical protective gloves uvex rubiflex S XG35B, Glove size: 8****Order data**

Order number	094752 8
GTIN	4048612024843
Item class	04W

**Description****Version:**

uvex rubiflex S XG35B. Lightweight knitted chemical protection gloves with innovative uvex Xtra Grip technology. These combine protection and a reliable grip with excellent wearing comfort – thanks to the cotton lining – and flexibility. Good resistance to many chemicals with very good resistance to greases and mineral oils.

Category III safety gloves.

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Permeation time for dimethyl sulphoxide 99 %	30-40 min
Permeation time for sodium hydroxide 40 %	>480 min
Permeation time for acetone 99 %	<10 min
Wet grip	very good
Glove size	8

Permeation time for acetonitrile 99 %	<10 min
Permeation time for cyclohexane 99 %	>480 min
Permeation time for sulphuric acid 96 %	30-40 min
Permeation time for methanol 99 %	10-30 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for sodium hydroxide 50 %	>480 min
Lining material	Cotton
Series	uvex rubiflex
Type of glove	Chemicals protection gloves
Protection category	Category III
Contents	10
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374	Type A (JKNOPT)
Resistance to chemicals	JKNOPT
EN 388	3121X
Material	Nitrile
Backing material	Cotton
Length	350 mm
Thickness	0.4 mm
Colour	black / blue
Application	reusable
Coating	Nitril
Coating variant	Full coating
Type of product	Chemicals protection gloves