



## Pair of chemical protective gloves Camatril® 730, Glove size: 11



### Order data

Order number	094748 11
GTIN	4008198773016
Item class	04Q

### Description

#### Version:

Category III safety gloves.

**Camatril® 730.** Nitrile gloves with velour cotton and a wide spectrum of chemical resistance characteristics. Good temperature resistance with at the same time good touch sensitivity. Absolutely free of silicones, no effect on paints. Approved for contact with foodstuffs.

#### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

### Technical description

Permeation time for acetonitrile 99 %	<10 min
Permeation time for sulphuric acid 96 %	60-120 min
Permeation time for sodium hydroxide 50 %	240-480 min
Permeation time for dimethyl sulphoxide 99 %	60-120 min
Permeation time for isopropanol 99 %	240-480 min
Permeation time for sulphuric acid 50 %	>480 min

Manufacturer's designation	Camatril 730
Permeation time for methanol 99 %	10-30 min
Permeation time for ethanol 95 %	60-120 min
silicone-free	yes
Wall thickness	0.4 mm
Permeation time for acetone 99 %	<10 min
Permeation time for sodium hydroxide 40 %	240-480 min
Permeation time for cyclohexane 99 %	>480 min
Glove size	11
Series	Camatril®
Type of glove	Chemicals protection gloves
Protection category	Category III
Contents	10
Glove characteristics	Foodstuffs certified
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Glove characteristics	free of latex
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374	Type A (AJKLOT)
Resistance to chemicals	AJKLOT
EN 388	3001X
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Application range	All-round
Length	310 mm
Thickness	0.4 mm
Colour	green
Application	reusable

Standard/regulation	EN 374
Type of product	Chemicals protection gloves