

**ASATEX****Pair of cold protection gloves 3677V, Glove size: 8****Order data**

Order number	094811 8
GTIN	4029201140823
Item class	09H

**Description****Version:**

**3677V.** Gloves with **very warm and pleasant acrylic lining.** Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

**Standard:**

**3677V.** Gloves with **very warm and pleasant acrylic lining.** Best grip in the wet thanks to HPT® -vinyl coating. Oil-repellent and grease-repellent.

**Application:**

For windy, cold or wet working conditions.

**Use of the advertising text:**

For windy, cold or wet working conditions.

**Standard:**

EN 388; EN 511

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Note re advertising text:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.  
Colour: black

**Technical description**

Glove size	8
Cold protection	good
DMF-free	yes
Lining material	Acrylic
Accuracy of fit	very good
Touch sensitivity	not available
silicone-free	yes
Oil grip	good
EN 388 tear propagation resistance	2
Material of coating	PVC
EN 388 penetration resistance	1
Wet grip	good
EN 388 cut resistance	2
Heat protection	not available
Breathability	not available
EN 388 abrasion resistance	3
Type of glove	Cold protection gloves
Protection category	Category II
Glove characteristics	DMF-free
Glove characteristics	Silicone-free
Contents	6
Application	reusable
Application range	All-round
EN 388:2016	3131X
EN 511	010
Backing material	Polyamide / acrylic
Coating	HPT/vinyl
Coating variant	3/4 coating
Colour	black

Weight	53 g
Type of product	Cold protection gloves