



## Nibblers, Type: 723241



### Order data

Order number	078111 723241
GTIN	4014586870069
Item class	03F

### Description

#### Version:

- **Very economical operating costs due to long working life of die and matrix.**
- **QuickIN quick-change system for quick die and matrix changing without tools**
- **Working direction can be changed without tools.**
- **Slim design ensures optimum handling even under difficult working conditions.**
- **Highly suitable for trapezoidal sheet up to 1.3 mm thick and up to 85 mm step depth.**

**Flexible nibblers with high manoeuvrability** for thin sheet metal, trapezoidal sheet, corrugated sheet and sections.

#### Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

### Technical description

maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	0.6 mm
Manufacturer's designation	BLK 1.3TE
Cutting width	4 mm
Power consumption	350 W
maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.3 mm
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Cutting speed	2.3 m/min

Weight	1.8 kg
Radius of the smallest curve	30 mm
Rate of strokes	1800 min <sup>-1</sup>
Power supply	Mains operated
Type of product	Nibblers