



Cordless sabre saw, Type: M18CSX



Order data

Order number	078220 M18CSX
GTIN	4002395160563
Item class	03L

Description

Version:

Milwaukee cordless sabre saw for working in difficult-to-access areas.

- **Electronic controls with steplessly variable stroke length and overload protection.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**

With **powerful brushless POWERSTATE™ motor.**

Supplied with:

Supplied with a carrying case / carrying wallet, 2 batteries, quick charger and saw blade.

Note:

Sabre saw blades can be found from No. 588600.

See No. 073810; 073811; 073814; 073815; 073816; 073829 for suitable spare batteries and chargers.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type HB 18 V

Manufacturer's designation: M18CSX-502X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 Ah

Battery voltage: 18 V

Stroke length: 28.6 mm

Technical description

Battery voltage	18 V
Special features	FIXTEC, LED

Battery capacity	5 Ah
Weight	4.1 kg
maximum vibration to EN	16.7 m/s ²
Stroke length	28.6 mm
Rate of strokes	0 - 3000 rpm
Manufacturer's designation	M18CSX-502X
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Packaging	Modular case (HD=Heavy Duty)
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC