



Deburring and chamfering machine, Type: EKF450



Order data

Order number	078121 EKF450
GTIN	4250187507243
Item class	07E

Description

Version:

Chamfering machine with smooth start-up and thermal overload protection for machining straight edges, internal and external radii and holes from 22 mm Ø. Fine adjustment permits light chamfering for deburring and also wide chamfering. With improved cutter head for reduced cutting forces. Chamfer 45° – width stepless 0 - 6 mm.

Supplied with:

Milling head, **3 carbide** inserts, swarf hook No. 084520 and transport case.

Note:

A component edge height of at least 2 mm is necessary to provide guidance.

Technical description

Width	138 mm
Height	295 mm
Weight	4 kg
Power consumption	1500 W

AC supply voltage	230 V
Manufacturer's designation	EKF450
Length	310 mm
maximum speed	6000 min ⁻¹
Chamfer	45°
Power supply	Mains operated
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Milling tool3-cutter Type ZFR450	078133 ZFR450
Carbide insert set, 3 pieces, SHM 200for steel Type SHM200	078128 SHM200
Spare screw for EKF inserts Version SCREW	078127 SCREW