

**3M****Welder's mask 3M™Speedglas™ 10 V, Colour: BLACK****Order data**

Order number	097905 BLACK
GTIN	4046719788804
Item class	040

**Description****Version:**

Entry-level model with variable **automatic welding filter** and 3 steps of sensitivity. The robust mask offers **reliable protection** and is suitable for occasional welding work, e.g. maintenance work. With **comfortable headband** and **exchangeable visor**. Can be combined as required with other personal protective equipment, such as safety glasses, or respirators. **Shade levels:** 10 – 12. **Shade level in the light state:** 3. With lithium 3 V battery (working life 1,500 hours). **Field of view of the welding filter:** 44 × 93 mm.

**Application:**

MIG/MAG welding and stick welding

**Standard:**

EN 175:B; EN 379; EN 166:BT

Switching time from bright to dark: 0.1 ms

Switching time from dark to bright: 40 - 250 ms

Classification to EN 379: 1 / 2 / 2 / 2

**Technical description**

Switching time from dark to bright	40 - 250 ms
------------------------------------	-------------

Classification to EN 379	1 / 2 / 2 / 2
Type	BLACK
Switching time from bright to dark	0.1 ms
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Type of product	Welder's mask