



Welder's mask, automatic 3M™ Speedglas™ 100 V, Colour: BLACK



Order data

Order number	097910 BLACK
GTIN	4046719712878
Item class	040

Description

Version:

Automatic welding mask with all the important basic functions. For reliable protection at an **excellent price-performance ratio**. With **comfortable headband** and **free-moving ratchet system** for precise adjustment of the fit. Delay function for individual determination of the brightening delay. **Increased shock resistance** to EN 175:B. Compatible with other personal protective equipment, such as dust masks. Exchangeable visor. **Shade levels: 8 - 12. Shade level in the light state: 3.** With lithium 3 V battery (working life 1,500 hours). **Field of view of the welding filter: 44 × 93 mm.**

Application:

MIG/MAG welding, stick welding and high-Ampère TIG welding

Standard:

EN 175:B; EN 379; EN 166:BT

Switching time from bright to dark: 0.1 ms

Switching time from dark to bright: 40 - 250 ms

Classification to EN 379: 1 / 2 / 2 / 2

Technical description

Switching time from dark to bright	40 - 250 ms
------------------------------------	-------------

Data sheet

Classification to EN 379	1 / 2 / 2 / 2
Type	BLACK
Switching time from bright to dark	0.1 ms
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Type of product	Welder's mask