



Welder's mask, automatic optrel® expert series, Type: E684



Order data

Order number	097950 E684
GTIN	7640429870421
Item class	09U

Description

Version:

The welder's mask E684 with stepless protection level adjustment, perfect view and true colour-rendition over the entire viewing area, particularly suitable for welding overhead. With individually adjustable **clamping angle** and **facility to adjust the sensitivity** to the working environment. With **opening delay** for gradual brightening from the darkened state. **Additional grinding mode**. With **dusk function** for a stepless transition from dark to light.

- **Shade levels: 5 - 13 with HD field of view. Steplessly adjustable with the rotary knob**
- **Shade level in the light state: 4**
- **With lithium 3 V battery (working life 3,000 hours)**
- **Colour: silver**
- **Field of view of the welding filter: 50 x 100 mm**

Application:

MIG/MAG welding. Stick welding, TIG welding, plasma welding

Standard:

EN 175; EN 379; EN 166

Supplied with:

1 outer visor, 1 storage bag.

Technical description

Type	E684
Switching time from dark to bright	100 - 2000 ms
Power supply	Battery-powered
Switching time from bright to dark	0.17 ms
Classification to EN 379	1 / 1 / 1 / 1
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Type of product	Welder's mask