

**Work jacket Highline, slate grey / black, Clothing size DE: 68****Order data**

Order number	091312 68
GTIN	4030913068107
Item class	06I

Description**Version:**

The fresh and modern **Highline** collection of high quality, non-abrasive, and non-shrinking fabric mixture in a three-colour look. Contrast colours of highly wear-resistant canvas. Hard-wearing three-row seams at all stress points. Many practical details such as mobile phone pockets and waistband adjustment.

Work jacket with expansion pleat in the back and elasticated cord in the waistband for optimum wearer comfort

- **Two breast pockets with flaps and hook and loop fastening.**
- **Concealed front zip fastener.**
- **Mobile phone pocket on the left sleeve.**
- **Two side patch pockets.**
- **Adjustable cuff with hook and loop fastening.**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Please check the QR code for further information on sizes and colours.

Jacket in colour combination **cornflower blue / navy** under No. 091311.

Washing: 60 °C coloureds

Technical description

Side pockets	patch
Collar	Elasticated cord in the waistband
Jacket closure	Zip fastener
Clothing size DE	68
Cuff	adjustable cuff with hook and loop fastener
Expansion pleats in the back.	yes
concealed placket	yes
Number of side pockets	2
Position of mobile phone pocket	on the left sleeve
Size FR	64
Number of breast pockets with flap and hook and loop fastening.	2
Series	Highline
Special service provision	Textile finishing
Gender	Gentlemen's
Fabric composition	65% polyester
Fabric composition	35% cotton
Material weight / fabric density	285 g/m ²
Clothing standard	UV standard 801
Clothing standard	Oeko-Tex Standard 100
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	hot, up to maximum 200 °C

Colour	slate grey / black
Type of product	Work jacket