



Carbide core drill Depth of cut 35 mm, Ø DC: 65mm



Order data

| | |
|--------------|---------------|
| Order number | 119000 65 |
| GTIN | 4014586240527 |
| Item class | 03G |

Description

Version:

High performance carbide core drill with QuickIN arbor.

Overall length: 77 mm for all cutter sizes.

Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

Supplied with:

Without centring pin.

Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories.

The centring pin No. 119019 is required when using the core drills 119010 and 119000.

Technical description

| | |
|--------------------------|----------|
| Nominal Ø D _c | 65 mm |
| Tool material | Carbide |
| Colour ring | without |
| Type of product | Hole saw |

User data

| | Suitability | V _c | ISO code |
|--|-------------|----------------|----------|
|--|-------------|----------------|----------|

| | |
|--------------------------------|---|
| Alu > 10% Si | suitable only under restricted conditions |
| Steel < 500 N/mm ² | suitable |
| Steel < 750 N/mm ² | suitable |
| Steel < 900 N/mm ² | suitable |
| Steel < 1100 N/mm ² | suitable |
| INOX < 900 N/mm ² | suitable |
| INOX > 900 N/mm ² | suitable |
| GG(G) | suitable |
| CuZn | suitable |
| Uni | suitable |
| Oil | suitable |
| wet maximum | suitable |
| wet minimum | suitable only under restricted conditions |
| dry | suitable |