



Carbide core drill Depth of cut 35 mm, Ø DC: 15mm



Order data

Order number	119000 15
GTIN	4014586240022
Item class	03G

Description

Version:

High performance carbide core drill with QuickIN arbor.

Overall length: 77 mm for all cutter sizes.

Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

Supplied with:

Without centring pin.

Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories.

The centring pin No. 119019 is required when using the core drills 119010 and 119000.

Technical description

Nominal Ø D _c	15 mm
Tool material	Carbide
Colour ring	without
Type of product	Hole saw

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable
Steel < 1100 N/mm ²	suitable
INOX < 900 N/mm ²	suitable
INOX > 900 N/mm ²	suitable
GG(G)	suitable
CuZn	suitable
Uni	suitable
Oil	suitable
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable