



## Carbide core drill Depth of cut 35 mm, Ø DC: 60mm



### Order data

Order number	119000 60
GTIN	4014586240473
Item class	03G

### Description

#### Version:

**High performance carbide** core drill with QuickIN arbor.

**Overall length: 77 mm** for all cutter sizes.

#### Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

#### Supplied with:

**Without** centring pin.

#### Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories.

The centring pin No. 119019 is required when using the core drills 119010 and 119000.

### Technical description

Nominal Ø D <sub>c</sub>	60 mm
Tool material	Carbide
Colour ring	without
Type of product	Hole saw

### User data

	Suitability	V <sub>c</sub>	ISO code
--	-------------	----------------	----------

Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm <sup>2</sup>	suitable
Steel < 750 N/mm <sup>2</sup>	suitable
Steel < 900 N/mm <sup>2</sup>	suitable
Steel < 1100 N/mm <sup>2</sup>	suitable
INOX < 900 N/mm <sup>2</sup>	suitable
INOX > 900 N/mm <sup>2</sup>	suitable
GG(G)	suitable
CuZn	suitable
Uni	suitable
Oil	suitable
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable