

duMONT

Keyway broach HSS Fit P9, Type: 6C1



Order data

| | |
|--------------|--------------|
| Order number | 290406 6C1 |
| GTIN | 662600888053 |
| Item class | 29J |

Description

Application:

For production of keyways to DIN 6885.

Supplied with:

Broaches including the necessary shims.

Note:

- Broaches for high tensile materials, increased number of passes or special applications available (on request).
- After first and second of three passes, back the broach off slightly – the broach will then align itself.
- Coated broaches and inch size broaches available on request.
- BROACHING PRESSES can be found in Volume 2 (Hand tools and metrology).
- Size 28; 32 and 36 available on request, on short lead times.

Technical description

| | |
|---------------------------|------------|
| Back width | 9.63 mm |
| Broaching length in steel | 10 - 64 mm |
| Broach length | 299 mm |

| | |
|--|------------|
| necessary broaching force for St50 and max. broaching length | 1000 kg |
| for bore Ø to DIN 6885 | 18 - 22 mm |
| Keyway width | 6 mm |
| Keyway depth | 2.8 mm |
| Number of passes | 2 |
| Tool material | HSS |
| Type of product | Broach |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Alu plastics | suitable only under restricted conditions | | |
| Aluminium (short chipping) | suitable | | |
| Alu > 10% Si | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable only under restricted conditions | | |
| INOX < 900 N/mm ² | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Graphite, GRP, CRP | suitable only under restricted conditions | | |
| Oil | suitable | | |

Accessories

Shim for keyway broach No. 290405 – 407 Type 6C1

290410 6C1