

**Garant****CaraFin flexible diamond polishing file, Grit: D64µm****Order data**

Order number	529115 D64
GTIN	4045197994660
Item class	51G

**Description****Version:**

Polishing file with **flexible metal base body**. Outer face of **resilient PU material**, one side coated with diamond grit. Very homogeneous surface roughness due to multi-crystalline diamonds.

**Advantage:**

Ancillary times for preparation and cleaning, such as are required when polishing pastes are used, are eliminated.

**Application:**

Ideal for polishing work on concave and convex surfaces. Suitable for **hard materials such as carbide, cast iron, hardened steels, ceramic** and non-ferrous metals.

**Technical description**

Grit	D64
Grit designation	Polishing
Grinding media	Diamond
Grinding medium code	D
Width	14 mm
Length	165 mm
Type of product	Diamond file

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		