

Garant**NC reamer set No. 162900 in a box H7, Number of reamers: 6****Order data**

Order number	162925 6
GTIN	4045197994813
Item class	110

Description**Version:**

Version suitable for NC similar to DIN 212 **with straight shank \varnothing** for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. For **highest concentricity** and **process reliability**. **No need to order special collets**. With long flutes and left-hand helix. Even number of teeth with irregular spacing. Size 3 with centring tip, from size 4 with centre holes at both ends.

Reamer manufacturing tolerance to DIN 1420 for H7 hole tolerance field.

Content:

1 pc. each NC reamer: Size 3; 4; 5; 6; 8; 10

Supplied with:

6-piece NC reamer set in a box.

Technical description

Number of reamers	6
Hole tolerance	H7
Tool material	HSS E
Standard	Manufacturer's standard

Shank	DIN 1835 A to h6
Application for type of drilling	for through holes
Type of product	Phillips bit

Accessories

NC reamerH7 Nominal Ø DC mm or inch 10	162900 10
NC reamerH7 Nominal Ø DC mm or inch 3	162900 3
NC reamerH7 Nominal Ø DC mm or inch 4	162900 4
NC reamerH7 Nominal Ø DC mm or inch 5	162900 5
NC reamerH7 Nominal Ø DC mm or inch 6	162900 6
NC reamerH7 Nominal Ø DC mm or inch 8	162900 8