



Climate measuring instrument Moisture / temperature set, Type: FT



Order data

Order number	474164 FT
GTIN	4029547019395
Item class	47B

Description

Version:

Testo 440 climate measuring instrument and moisture / temperature probe **for measuring moisture and temperature in stores, cold rooms and work rooms, together with air ducts.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Testo 440 climatic measuring instrument No. 474141 size 440, 3× mignon batteries type AA, USB cable, moisture and temperature probe No. 474148 size FT, case No. 474161 size K and calibration certificate.

Technical description

Error limit relative humidity	±2 %
Error limit temperature	±0.5 °C
Temperature measurement range	-20 - 70 °C
Relative humidity measurement range	0 - 100 %
IP Index of Protection	IP 54

Power supply	Battery-powered
Battery type	Mignon, AA
Number of batteries contained	3
Calibration	Price on request
Interface	USB interface
Interface	Bluetooth interface
Type of product	Humidity and temperature sensor

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------