



Cordless pop rivet tool M12BPRT, Type: M12BPRT



Order data

Order number	770450 M12BPRT
GTIN	4058546223502
Item class	03L

Description

Version:

Cordless tool for flexible use.

Advantage:

- LED illumination of the working area.
- Integral belt clip.

Supplied with:

Supplied with Li-ion battery No. 073814 MB12 and charger in a plastic case, nozzles 2.4, 3.2, 4.0, 4.8 mm.

Note:

See No. 073814, 073815, 073829, 073839 and 073840 for suitable spare batteries and chargers. A version without battery and without charger can be found under No. 770450 M12BPRT-0.

Technical description

for pop rivets in all materials up to	4.8 mm
Setting force	9000 N
Tool stroke	20.32 mm

Weight including rechargeable battery	2.1 kg
Battery voltage	12 V
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Battery capacity	2 Ah
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Modular case (HD=Heavy Duty)
Type of product	Pop riveter

Accessories

Li-ion system M12B6 Battery type MB12	073829 MB12
Li-ion system M12B4 Battery type MB12	073815 MB12
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Jaws set Type 1	770452 1
Battery starter set Type M12NRG4	073839 M12NRG4
Spare mouthpiece set4 pieces Number of pieces 4	770451 4
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC