



LED-EX headband lamp with battery, Type: EXH8



Order data

Order number	081474 EXH8
GTIN	4058205007412
Item class	04B

Description

Version:

Explosion-proof headband lamp, tested to the applicable ATEX guidelines.

Headband lamp, very comfortable to wear, focussable, with red backlight. Comfortable "Magnetic Switch" for easy operation even when wearing gloves and protective equipment.

Headlamp, very comfortable to wear, focussable, with red backlight.

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with batteries (3 × AA).

IP Index of Protection: IP 68

Tool properties: Suitable for EX areas

Manufacturer's designation: EXH8

ATEX zone: Zone 0

ATEX zone: Zone 20

Illumination: 180 lm

Illumination step 2: 50 lm

Working life: 15 h

Technical description

Data sheet

Colour of housing	black
Advanced Focus System (AFS)	yes
ATEX zone	Zone 0
ATEX zone	Zone 20
Illumination	180 lm
Manufacturer's designation	EXH8
Power supply	Battery-powered
Battery type	Mignon, AA
Number of batteries contained	3
Lighting life stage 2	40 h
Head Ø	41 mm
Illumination range	65 - 120 m
IP Index of Protection	IP 68
Weight	345 g
Including belt pocket	no
Illumination step 2	50 lm
rechargeable	no
Tool properties	Suitable for EX areas
Working life	15 h
Type of product	Headlamp

Accessories

Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline manganese battery set International size LR6	081558 LR6
Alkaline-manganese batteries International size LR6	081556 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081552 LR6
Alkaline manganese battery set International size LR6	081557 LR6

Alkaline-manganese batteries International size LR6	081551 LR6
Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081554 LR6