



LED-EX torch with battery, Type: EX7



Order data

Order number	081484 EX7
GTIN	4058205001243
Item class	04B

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

The lamps of the new LED Lenser EX series are certified both for maximum dustproof and waterproof qualities. Torch with patented Advanced Focus System for focussing the light beam. Comfortable "Magnetic Switch" for easy operation even when wearing gloves and protective equipment.

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Battery type	Micro, AAA
Manufacturer's designation	EX7
Number of batteries contained	3
Illumination	60 - 200 lm
Illumination time	16 - 45 h
IP Index of Protection	IP 68
Weight	232 g
Including belt pocket	no
Head Ø	41 mm

Colour of housing	yellow
ATEX zone	Zone 0
ATEX zone	Zone 20
Advanced Focus System (AFS)	yes
Overall length	161 mm
Tool properties	Suitable for EX areas
Illumination range	70 - 120 m
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3