



## LED torches, Manufacturer's designation: P5R



### Order data

Order number	081485 P5R
GTIN	4058205009874
Item class	04B

### Description

#### Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All these high-class torches incorporate the patented **Advanced Focus System**.

High-performance line of LED LENSES for general- purpose use. Drop tested from a 1 m height.

- **Advanced Focus System (AFS)**

**The Advanced Focus System is a combination of lens and reflector, thus incorporating the advantages of both systems. The result is an outstanding concentration of light in focus, together with a largely homogeneous unfocussed light beam. This makes the AFS one of the best focussing systems in the world for LED lamps.**

- **Rapid Focus**

**Conventional focussing systems with twist knobs must be operated manually with both hands. Rapid Focus, on the other hand, allows quick adjustment of the light beam with only one hand.**

#### Supplied with:

Supplied with USB cable and wall attachment (Floating Charge System), USB charging capability.

#### Note:

In general, the manufacturer provides a warranty on this product of **five years** (seven years with online registration).

Illumination: 420 lm

Illumination step 2: 20 lm

Working life: 15 h

Lighting life stage 2: 15 h

Advanced Focus System (AFS): yes

Rapid Focus: yes

## Technical description

Advanced Focus System (AFS)	yes
Including belt pocket	yes
Manufacturer's designation	P5R
Illumination step 2	20 lm
Working life	15 h
Weight	75 g
Illumination	420 lm
Head Ø	26 mm
Lighting life stage 2	15 h
Rapid Focus	yes
Number of rechargeable batteries contained	1
Overall length	117 mm

## Accessories

Replacement battery Type P5R.2	081482 P5R.2
--------------------------------	--------------