

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M47X0,5****Order data**

| | |
|--------------|----------------|
| Order number | 130011 M47X0,5 |
| GTIN | 4062406017811 |
| Item class | 10N |

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 250 mm

Shank $\varnothing D_s$: 36 mmShank square \square : 29 mmTapping hole \varnothing : 46.5 mm**Technical description**

| | |
|----------------------------|---------|
| Tapping hole \varnothing | 46.5 mm |
| Standard | DIN 376 |
| Number of clamping slots | 4 |
| Shank $\varnothing D_s$ | 36 mm |
| Tool material | HSS E |
| Overall length L | 250 mm |

| | |
|----------------------------------|--|
| Thread Ø | 47 mm |
| Number of cutting edges Z | 4 |
| Thread pitch | 0.5 mm |
| Shank square □ | 29 mm |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Thread depth | 117.5 mm |
| Thread type | MF-LH |
| Thread size | M47×0.5 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |