

Garant**Left-hand thread through hole machine tap, uncoated, Type: 1/4-28****Order data**

Order number	130031 1/4-28
GTIN	4062406036812
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 3 pcs.
Special / custom-made product - return not possible
Thread type: UNF-LH
Tool material: HSS E
Standard: DIN 371
Threads per inch: 28
Thread \varnothing : 6.35 mm
Overall length L: 80 mm
Shank \varnothing D_s: 7 mm
Shank square \square : 5.5 mm
Tapping hole \varnothing : 5.5 mm

Technical description

Thread \varnothing	6.35 mm
Standard	DIN 371
Thread depth	19.05 mm
Thread pitch	0.907 mm
Tool material	HSS E
Number of clamping slots	3
Number of cutting edges Z	3

Threads per inch	28
Shank $\varnothing D_s$	7 mm
Shank square \square	5.5 mm
Tapping hole \varnothing	5.5 mm
Overall length L	80 mm
Thread type	UNF-LH
Thread size	1/4-28 UNF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap