

**HOLEX®**
**Side lock arbor Form ADB with cooling channels, SK 40 short, Clamping range  
 Ø D1: 14 mm**

**Order data**

Order number	300215 14
GTIN	4045197700971
Item class	32A

**Description**
**Version:**

With Balluffchip bore.

**With cooling channels.**
**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 50 mm

External Ø D: 44 mm

Spare clamping screw 309900: 12

**Technical description**

Spare clamping screw 309900	12
Clamping Ø D <sub>1</sub>	14 mm
Overhang dimension A	50 mm
External Ø D	44 mm
Adapter	SK 40 short
Norm	DIN 6359
Arbor standard	DIN 69871

Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC

## Accessories

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
Pull stud sealed suitable for steep tapers 40	308660 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308820 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK	308830 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
	308700 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK

308812 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40

308605 40

Pull stud 90° sealed suitable for steep tapers 40

308790 40

Pull stud sealed, form B suitable for steep tapers 40

308620 40

Pull stud 45° sealed suitable for steep tapers 40

308760 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40

308806 40

Pull stud Form A suitable for steep tapers 40

308600 40

Pull stud 60° sealed suitable for steep tapers 40

308785 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

308720 40