

**HOLEX®**
**Side lock arbor Form ADB with cooling channels, SK 40 A = 100, Clamping range  $\varnothing$  D1: 16 mm**

**Order data**

Order number	300265 16
GTIN	4045197701190
Item class	32A

**Description**
**Version:**

With Balluffchip bore.

**With cooling channels.**
**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External  $\varnothing$  D: 48 mm

Spare clamping screw 309900: 16

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	16 mm
Spare clamping screw 309900	16
External $\varnothing$ D	48 mm
Adapter	SK 40 A = 100
Norm	DIN 6359
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB

Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC

## Accessories

Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK	308830 40
Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Pull stud Form A suitable for steep tapers 40	308600 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud sealed suitable for steep tapers 40	308660 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308820 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40