

**Garant**
**Shrink-fit chuck with cooling channel bores and strengthened walls, HSK-A 63  
A = 120, Clamping range Ø D1: 10mm**

**Order data**

Order number	308297 10
GTIN	4045197701589
Item class	31A

**Description**
**Version:**

- **High-temperature steel.**
- **Integral tool length adjustment, adjustment track 10 mm.**
- **For HSS and carbide.**
- **Shanks hard turned (for smooth running!).**
- **With Balluffchip bore**
- **Bead-blasted**
- **With cooling channel bores, tapped for plugging.**

**Advantage:**

**Optimised design. Vibration-damping effect, better workpiece surface finish, protects spindle and tool.**

**Application:**

For clamping tools with parallel shank to h6 tolerance. Suitable for inductive, contact and hot-air shrink units.

**Optional extras:**

Shrink-fit chuck adaptors No. 302410 – 302416. Shrink-fit units, accessories No. 354210 – 304755.

Cooling channel bore: lockable

Clamping Ø D<sub>1</sub>: 10 mm

Overhang dimension A: 120 mm

External Ø D: 52.5 mm

Ø D<sub>2</sub>: 24 mm

Ø D<sub>3</sub>: 32.7 mm

## Technical description

Ø D <sub>3</sub>	32.7 mm
Clamping Ø D <sub>1</sub>	10 mm
Ø D <sub>2</sub>	24 mm
Overhang dimension A	120 mm
External Ø D	52.5 mm
Cooling channel bore	lockable
Adapter	HSK-A 63 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Shrink-fit chuck

## Accessories

Cooling adapter short 4.5° for clamping Ø 9,1-12 mm	354235 9,1-12
Cooling unit Type CU1	354215 CU1
Subframe cupboard	354290
Screening plate for coil SU1 for clamping Ø 6-12 mm	354240 6-12
Cooling adapter long 4.5° for clamping Ø 9,1-12 mm	354236 9,1-12
Shrink-fit unit Type SU1	354210 SU1