

FAHRION®
FAHRENDEN PROTEKTION**ER collet, ER 25, Nominal clamping Ø d: 2mm****Order data**

| | |
|--------------|---------------|
| Order number | 308941 2 |
| GTIN | 2050001767837 |
| Item class | 39Y |

Description**Version:**

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

The **collet clamping Ø range is always up to 1 mm less than nominal**, e.g. Ø 10 – 9 mm, **except for Ø 1, 1.5 and 2 (where it is only 0.5 mm).**

Technical description

| | |
|----------------------|-------------|
| Nominal clamping Ø d | 2 mm |
| Adapter | ER 25 |
| Standard | ISO 15488-B |
| Concentricity | ≤ 5 µm |
| Type | 430 E |
| External Ø D | 26 mm |
| Overall length L | 34 mm |

Type of product

Collet