


FAHRION®
FAHRENDEN PROTEKTION
ER collet, ER 32, Nominal clamping Ø d: 10mm

Order data

Order number	308981 10
GTIN	2050001766489
Item class	39Y

Description
Version:

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

The **collet clamping Ø range** is **always up to 1 mm less than nominal**, e.g. Ø 10 – 9 mm, **except for Ø 1, 1.5 and 2 (where it is only 0.5 mm)**.

Technical description

Nominal clamping Ø d	10 mm
Adapter	ER 32
Standard	ISO 15488-B
Concentricity	≤ 5 µm
Type	470 E
External Ø D	33 mm
Overall length L	40 mm

Type of product

Collet