




ER collet, ER 40, Nominal clamping \varnothing d: 7mm



Order data

Order number	308990 7
GTIN	2050001765772
Item class	39Y

Description

Version:

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

The **collet clamping \varnothing range** is **always up to 1 mm less than nominal**, e.g. \varnothing 10 – 9 mm, **except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm)**.

Technical description

Nominal clamping \varnothing d	7 mm
Adapter	ER 40
Standard	ISO 15488-B
Concentricity	$\leq 5 \mu\text{m}$
Type	472 E
External \varnothing D	41 mm
Overall length L	46 mm

Type of product

Collet