



ER collet, ER 20, Nominal clamping \varnothing d: 13mm



Order data

Order number	308911 13
GTIN	2050001766588
Item class	39Y

Description

Version:

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

The **collet clamping \varnothing range** is **always up to 1 mm less than nominal**, e.g. \varnothing 10 – 9 mm, **except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm).**

Technical description

Nominal clamping \varnothing d	13 mm
Adapter	ER 20
Standard	ISO 15488-B
Concentricity	$\leq 5 \mu\text{m}$
Type	428 E
External \varnothing D	21 mm
Overall length L	31.5 mm
Type of product	Collet

