



## ER collet, ER 20, Nominal clamping $\varnothing$ d: 6mm



### Order data

Order number	308911 6
GTIN	2050001764690
Item class	39Y

### Description

#### Version:

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

#### Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

#### Note:

The **collet clamping  $\varnothing$  range** is **always up to 1 mm less than nominal**, e.g.  $\varnothing$  10 – 9 mm, **except for  $\varnothing$  1, 1.5 and 2 (where it is only 0.5 mm).**

### Technical description

Nominal clamping $\varnothing$ d	6 mm
Adapter	ER 20
Standard	ISO 15488-B
Concentricity	$\leq 5 \mu\text{m}$
Type	428 E
External $\varnothing$ D	21 mm
Overall length L	31.5 mm
Type of product	Collet

