

FAHRION®
FAHRENDEN PRESSION
ER collet HP, ER 16, Nominal clamping \varnothing d: 5mm

Order data

| | |
|--------------|---------------|
| Order number | 309370 5 |
| GTIN | 2050001766175 |
| Item class | 39Y |

Description
Version:

System concentricity and repetition accuracy **3 μ m** ($3 \times D$, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for:

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

Technical description

| | |
|----------------------------------|----------------|
| Nominal clamping \varnothing d | 5 mm |
| Adapter | ER 16 |
| Standard | ISO 15488-B |
| Concentricity | $\leq 2 \mu$ m |
| Type | 426 E |

| | |
|--------------------------|---------|
| External \varnothing D | 17 mm |
| Overall length L | 27.5 mm |
| Type of product | Collet |